

## Check Your Luggage With Confidence

The next time you fly use a Voltage Valet *Travel Sentry™ Approved Combination Lock* to safely lock your luggage. Airline check-in personnel and the TSA have been trained to recognize locks with the *Travel Sentry* mark and know that your luggage can remain locked during check-in. If an inspection is necessary during screening, TSA personnel will use a *Travel Sentry* secured access device to open and relock your luggage.

### Combination Lock Instructions:

The Voltage Valet Combination Lock is preset at the factory to open at 0-0-0. To set your own combination, follow these simple steps:

1. Set the dials between the arrows to the opening combination, 0-0-0, and pull up the shackle from the locking position.
2. Turn the shackle 180 degrees (1/2 turn) and push in.
3. Hold shackle depressed and turn 90 degrees (1/4 turn) in either direction.
4. Set the dials to your own combination.
5. Without moving the dials, return the shackle to the 180 degree position. Pull up the shackle and return it to the original locking position. Your combination is now set.
6. To lock, push the shackle in at the locking position and rotate one or more of the dials.

### TSA Search Indicator:

The TSA Search Indicator is preset to Green at the factory. It will turn from Green to Red if the lock is opened by the TSA. If your TSA Search Indicator is Red when you receive your luggage, immediately inspect it for the **TSA Notification of Baggage Inspection**. If none is found, take your luggage to your airline's baggage claim office to determine if anything is missing or if anything has been added to your luggage. To reset the TSA Search Indicator:

1. Set the dials to the opening combination and pull up the shackle.
2. Turn the shackle 180 degrees (1/2 turn) and push the shackle in resetting the search indicator to Green.
3. Pull up the shackle and the lock is ready for use.

**Voltage Valet Division**  
**Hybrinetics, Inc.**  
**225 Sutton Place**  
**Santa Rosa, CA 95407**  
**Made in Taiwan**

**Model 2TL31**

Patent No:  
US 6.877.345  
US 7.007.521